

RACKPOWER DOOR SWITCH SENSOR



Door Switch Sensor with Magnetic Switch for nVent SCHROFF RackPower PDU's.

FEATURES

Door Switch Sensor with Magnetic Switch

1 m Cable to Sensor box with integrated magnet for easy mounting and 1 m connection Cable

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Operating Temperature range 0 to 65 °C

SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type | Product Family | Works With | Package Quantity | Height | Removable Input Cable |
|----------------|--------------|----------------|------------|------------------|--------|-----------------------|
| EA9109 | Sensor | Enlogic | RackPower | 1 | 270mm | No |

Table 2/2

| Catalog Number | Plug Type |
|----------------|-----------|
| EA9109 | RJ45 |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER