



NVENT CADDY MACROFIX NON-INSULATED VENTILATION DUCT CLAMP



CERTIFICATIONS



FEATURES

Complete hanger assembly comes out of the box ready to install (sizes up to 600 mm)

Increased opening angle easily accommodates all standard-sized spiral ducts (sizes up to 600 mm)

Quick locking system prevents the hanger from accidentally opening when duct is moved or adjusted (sizes up to 600 mm)

Quick locking system easily closes with one hand (sizes up to 600 mm)

Thread impression retains quick locking captive screw and prevents it from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Combination nut can be attached to M8 or M10 threaded rod, simplifying material handling

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Temperature: -50 to 110 °C

Table 1/2


Catalog Number	Article Number	Outer Diameter (OD)	Rod Size (RS)	Width (W)	Thickness (T)	Screw Diameter (Sc)
MFVN0100EG	586503	100 mm	8, 10"	20 mm	1 mm	6
MFVN0125EG	586505	125 mm	8, 10"	20 mm	1 mm	6
MFVN0140EG	586506	140 mm	8, 10"	20 mm	1 mm	6
MFVN0150EG	586507	150 mm	8, 10"	20 mm	1 mm	6
MFVN0160EG	586508	160 mm	8, 10"	20 mm	1 mm	6
MFVN0180EG	586509	180 mm	8, 10"	20 mm	1 mm	6
MFVN0200EG	586510	200 mm	8, 10"	20 mm	1 mm	6
MFVN0224EG	586511	224 mm	8, 10"	21 mm	1.25 mm	6
MFVN0250EG	586512	250 mm	8, 10"	21 mm	1.25 mm	6
MFVN0315EG	586515	315 mm	8, 10"	21 mm	1.25 mm	6
MFVN0355EG	586516	355 mm	8, 10"	21 mm	1.25 mm	6
MFVN0400EG	586517	400 mm	8, 10"	21 mm	1.25 mm	6
MFVN0450EG	586518	450 mm	8, 10"	21 mm	1.5 mm	6
MFVN0500EG	586519	500 mm	8, 10"	21 mm	1.5 mm	6
MFVN0630EG	586522	630 mm	8, 10"	23 mm	1.75 mm	6
MFVN0800EG	586524	800 mm	8, 10"	23 mm	1.75 mm	6
MFVN1000EG	586526	1000 mm	8, 10"	23 mm	2 mm	6

Table 2/2

Catalog Number	Article Number	Screw Length (L)	Angle (a)	Static Load (F)	Certifications
MFVN0100EG	586503	27mm	80 °	775N	ITB, RAL-GZ 655
MFVN0125EG	586505	27mm	80 °	775N	ITB, RAL-GZ 655
MFVN0140EG	586506	40mm	80 °	775N	ITB, RAL-GZ 655
MFVN0150EG	586507	40mm	80 °	775N	ITB, RAL-GZ 655
MFVN0160EG	586508	40mm	80 °	775N	ITB, RAL-GZ 655
MFVN0180EG	586509	40mm	80 °	775N	ITB, RAL-GZ 655
MFVN0200EG	586510	40mm	80 °	775N	ITB, RAL-GZ 655
MFVN0224EG	586511	40mm	80 °	1000N	ITB, RAL-GZ 655
MFVN0250EG	586512	40mm	80 °	1000N	ITB, RAL-GZ 655
MFVN0315EG	586515	40mm	80 °	1000N	ITB, RAL-GZ 655
MFVN0355EG	586516	40mm	80 °	1000N	ITB, RAL-GZ 655
MFVN0400EG	586517	40mm	80 °	1000N	ITB, RAL-GZ 655
MFVN0450EG	586518	40mm	80 °	900N	

CatalogNumber	Article Number	Screw Length (L)	Angle (a)	Static Load (F)	Certifications
MFVN0500EG	586519	40mm	80 °	900N	
MFVN0630EG	586522	40mm		1150N	ITB
MFVN0800EG	586524	40mm		1150N	
MFVN1000EG	586526	40mm		1400N	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER