

RACKPOWER DRY CONTACT CABLE

CATALOG NUMBER

EA9110



Dry Contact Cable to connect I/O sensors e.g. smoke for nVent SCHROFF RackPower PDU's.

FEATURES

Dry Contact Cable to connect I/O sensors e.g. smoke

1 m Cable to Sensor box with integrated magnet for easy mounting and 1.8 m connection Cable

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Operating Temperature range 0 to 65 °C

ATRIBUTOS DEL PRODUCTO

Product Type: Sensor

Works With: RackPower

Height: 260mm

Package Quantity: 1

Plug Type: RJ45

Product Family: Enlogic

Removable Input Cable: No

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER