

FRONT PANEL, ANODIZED WITH UNTREATED EDGES, UNSHIELDED

Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.



CERTIFICATIONS



CARACTERÍSTICAS

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

ESPECIFICACIONES

Table 1/3

Número de catálogo	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30818-271	Ninguno	No	Anodizado	Anodizado	No	84 HP
30818-310	Ninguno	No	Anodizado	Anodizado	No	42 HP
30818-331	Ninguno	No	Anodizado	Anodizado	No	63 HP
30818-352	Ninguno	No	Anodizado	Anodizado	No	84 HP
30818-434	Ninguno	No	Anodizado	Anodizado	No	84 HP
30818-556	Ninguno	No	Anodizado	Anodizado	No	42 HP
30818-577	Ninguno	No	Anodizado	Anodizado	No	63 HP
30818-598	Ninguno	No	Anodizado	Anodizado	No	84 HP

Número de catálogo	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30810-433	Ninguno	No	Anodizado	Anodizado	No	2 HP
30818-747	Ninguno	Sí	Anodizado	Anodizado	No	2 HP
30818-272	Ninguno	No	Anodizado	Anodizado	No	3 HP
30818-273	Ninguno	No	Anodizado	Anodizado	No	4 HP
30818-274	Ninguno	No	Anodizado	Anodizado	No	5 HP
30818-275	Ninguno	No	Anodizado	Anodizado	No	6 HP
30818-276	Ninguno	No	Anodizado	Anodizado	No	7 HP
30818-277	Ninguno	No	Anodizado	Anodizado	No	8 HP
30818-279	Ninguno	No	Anodizado	Anodizado	No	10 HP
30818-281	Ninguno	No	Anodizado	Anodizado	No	12 HP
30818-282	Ninguno	No	Anodizado	Anodizado	No	14 HP
30818-289	Ninguno	No	Anodizado	Anodizado	No	21 HP
30818-296	Ninguno	No	Anodizado	Anodizado	No	28 HP
30818-518	Ninguno	No	Anodizado	Anodizado	No	4 HP
30818-519	Ninguno	No	Anodizado	Anodizado	No	5 HP
30818-520	Ninguno	No	Anodizado	Anodizado	No	6 HP
30818-521	Ninguno	No	Anodizado	Anodizado	No	7 HP
30818-522	Ninguno	No	Anodizado	Anodizado	No	8 HP
30818-524	Ninguno	No	Anodizado	Anodizado	No	10 HP
30818-526	Ninguno	No	Anodizado	Anodizado	No	12 HP
30818-528	Ninguno	No	Anodizado	Anodizado	No	14 HP
30818-530	Ninguno	No	Anodizado	Anodizado	No	16 HP
30818-535	Ninguno	No	Anodizado	Anodizado	No	21 HP
30818-542	Ninguno	No	Anodizado	Anodizado	No	28 HP

Table 2/3						
Número de catálogo	Package Quantity	Altura	Product Type	Tipo	Rack Height	Ancho
30818-271	1	84 mm	Front Panel	Front Panel without Handle	2 U	426.4 mm
30818-310	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	213 mm
30818-331	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	319.7 mm
30818-352	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	426.4 mm

Número de catálogo	Package Quantity	Altura	ProductType	Tipo	Rack Height	Ancho
30818-434	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	426.4 mm
30818-556	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	213 mm
30818-577	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	319.7 mm
30818-598	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	426.4 mm
30810-433	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	9.8 mm
30818-747	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	9.8 mm
30818-272	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	14.9 mm
30818-273	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30818-274	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	25 mm
30818-275	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	30.1 mm
30818-276	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	35.2 mm
30818-277	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	40.3 mm
30818-279	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	50.5 mm
30818-281	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	60.6 mm
30818-282	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	70.8 mm
30818-289	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	106.3 mm
30818-296	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	141.9 mm
30818-518	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	20 mm
30818-519	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	25 mm
30818-520	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	30.1 mm

Número de catálogo	Package Quantity	Altura	ProductType	Tipo	Rack Height	Ancho
30818-521	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	35.2 mm
30818-522	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	40.3 mm
30818-524	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	50.5 mm
30818-526	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	60.6 mm
30818-528	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	70.8 mm
30818-530	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	80.9 mm
30818-535	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	106.3 mm
30818-542	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	141.9 mm

Table 3/3			
Número de catálogo	Cumple con	Montaje	Material
30818-271	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-310	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-331	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-352	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-434	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-556	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-577	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-598	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30810-433	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-747	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-272	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio

Número de catálogo	Cumple con	Montaje	Material
30818-273	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-274	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-275	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-276	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-277	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-279	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-281	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-282	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-289	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-296	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-518	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-519	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-520	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-521	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-522	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-524	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-526	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-528	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-530	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-535	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio
30818-542	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER