


SOCKET STRIP, IEC C19



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C19 outlets.

CERTIFICATIONS



FEATURES

Socket strips with C19 IEC sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

Connecting cable 2 m, with connector in accordance with IEC 60309

Mounting height 1 U

SPECIFICATIONS

Table 1/2

Número de catálogo	Tipo de producto	Tipo de toma de corriente	Número de tomas de corriente	Switched Outlets	Color	Voltaje de CA
60110-280	Socket Strip	IEC C19	8	No	Grey	230V
60110-281	Socket Strip	IEC C19	12	No	Grey	230V
60110-282	Socket Strip	IEC C19	12	No	Grey	230V

Table 2/2

Número de catálogo	Altura	Longitud	Profundidad	Acabado	Material	Cantidad de paquetes
--------------------	--------	----------	-------------	---------	----------	----------------------

60110-280	44mm	438.5mm	44mm	Anodized	Aluminio, Poliamida	1
60110-281	44mm	947.5mm	44mm	Anodized	Aluminio, Poliamida	1
60110-282	44mm	947.5mm	44mm	Anodized	Aluminio, Poliamida	1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER