

## 19" FAN UNIT, 1 U, SPEED CONTROL AND MONITORING

Fan Unit for installation into a 1 U space within the Cabinet.



### CERTIFICATIONS



### CARACTERÍSTICAS

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

### ESPECIFICACIONES

Table 1/1

| Número de catálogo | Input Voltage DC | Product Type | Input Voltage AC | Accessory Type | Certificaciones |
|--------------------|------------------|--------------|------------------|----------------|-----------------|
| 10713-098          | 24 V min         | Fan Unit     |                  | Fan unit, 19"  | RoHS, CE, EAC   |
| 10713-099          | 24 V min         | Fan Unit     |                  | Fan unit, 19"  | RoHS, CE, EAC   |
| 19713-006          |                  | Fan Unit     | 230 V min        | Fan unit, 19"  | RoHS, EAC       |
| 19713-121          |                  | Fan Unit     | 230 V min        | Fan unit, 19"  | RoHS, EAC       |

## ADVERTENCIA

---

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**