


GUIDE RAIL WITH CODING FOR COMPACTPCI/ VME64X, PC



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

CERTIFICATIONS



FEATURES

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to a optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

Storage temperature: from -40 °C ... 130 °C

SPECIFICATIONS

Table 1/2

Número de catálogo	Tipo	Funciona con	Board Depth	Material	Color	Cantidad de paquetes
64568-089	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic	Red	1

Número de catálogo	Tipo	Funcionacon	Board Depth	Material	Color	Cantidad de paquetes
64568-090	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic	Grey	1
64568-085	Coding	Subracks, Cases, 19" Chassis, Systems	70mm	Fiber-Reinforced Plastic	Red	1
64568-086	Coding	Subracks, Cases, 19" Chassis, Systems	70mm	Fiber-Reinforced Plastic	Grey	1
64568-091	Coding	Subracks, Cases, 19" Chassis, Systems	220mm	Fiber-Reinforced Plastic	Red	1
64568-092	Coding	Subracks, Cases, 19" Chassis, Systems	220mm	Fiber-Reinforced Plastic	Grey	1
64568-111	Coding	Subracks, Cases, 19" Chassis, Systems	220mm	Fiber-Reinforced Plastic, Aluminum	Red, Silver	1
64568-109	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic, Aluminum	Red, Silver	1
64568-110	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	1
64568-112	Coding	Subracks, Cases, 19" Chassis, Systems	220mm	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	1
24568-356	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic	Red	10
24568-357	Coding	Subracks, Cases, 19" Chassis, Systems	70mm	Fiber-Reinforced Plastic	Red	10

Número de catálogo	Tipo	Funcionacon	Board Depth	Material	Color	Cantidad de paquetes
24568-358	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic	Grey	10
24568-360	Coding	Subracks, Cases, 19" Chassis, Systems	70mm	Fiber-Reinforced Plastic	Grey	10
24568-331	Coding	Subracks, Cases, 19" Chassis, Systems	280mm	Fiber-Reinforced Plastic, Aluminum	Red, Silver	10
24568-332	Coding	Subracks, Cases, 19" Chassis, Systems	340mm	Fiber-Reinforced Plastic, Aluminum	Red, Silver	10
24568-341	Coding	Subracks, Cases, 19" Chassis, Systems	280mm	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	10
24568-342	Coding	Subracks, Cases, 19" Chassis, Systems	340mm	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	10

Table 2/2			
Número de catálogo	Cumple con	Ancho de la ranura	Acabado
64568-089	EN 45545-2	2	
64568-090	EN 45545-2	2	
64568-085	EN 45545-2	2	
64568-086	EN 45545-2	2	
64568-091	EN 45545-2	2	
64568-092	EN 45545-2	2	
64568-111	EN 45545-2	2.5	
64568-109	EN 45545-2	2.5	
64568-110	EN 45545-2	2.5	
64568-112	EN 45545-2	2.5	
24568-356	EN 45545-2	2	
24568-357	EN 45545-2	2	
24568-358	EN 45545-2	2	
24568-360	EN 45545-2	2	

Número de catálogo	Cumple con	Ancho de la ranura	Acabado
24568-331	EN 45545-2	2.5	Anodized
24568-332	EN 45545-2	2.5	Anodized
24568-341	EN 45545-2	2.5	Anodized
24568-342	EN 45545-2	2.5	

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER