

BASIC PDU, EB0403, 400 VAC, 3-PH, 16 A

CATALOG NUMBER

EB0403



Modular, compact PDU. Ultra-Low Profile Design

FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

ATRIBUTOS DEL PRODUCTO

Familia de productos: Enlogic

Tipo: Basic PDU

Tipo de producto: Socket Strip

Tipo de toma de corriente: (36) C13; (6) C19

Número de tomas de corriente: 42

Switched Outlets: No

Disyuntores: No Circuit Breaker

Circuit Breaker Quantity: 0

Calificación actual: 11A

Input Cable Length: 3m

Input Cable Location: Top Feed

Input Current: 16 A

Voltaje de entrada: 380-415 VAC, 3 PH

Max Power Input: 11.0 kVA

Tensión nominal: 415V

On/Off Switch Included: No

Output Voltage: 230VAC

Plug Type: IEC 60309 516P6 (IP44)

Unidades de rack: 0U

Removable Input Cable: No

Metering Type: Ninguno

Material: Acero

Acabado: Powder Coated

Color: Negro

Altura: 1490mm

Ancho: 52mm

Profundidad: 53mm

Peso: 6.11kg

Cantidad de paquetes: 1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER