

## FRONT PANEL, REFROFIT SHIELDING



Flat front panel. Shieldable with stainless steel EMC gasket.

### CERTIFICATIONS



### CARACTERÍSTICAS

For stainless steel EMC gasket

Aluminum, 2.5 mm, front anodized, conductive

### ESPECIFICACIONES

Table 1/3

| Número de catálogo | EMC Gasket Type  | Treated Edges | Front Finish | Rear Finish | EMC Shielding      | Rack Width |
|--------------------|------------------|---------------|--------------|-------------|--------------------|------------|
| 20846-437          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 42 HP      |
| 20846-438          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 63 HP      |
| 20846-453          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 42 HP      |
| 20846-454          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 63 HP      |
| 30846-676          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 84 HP      |

| Número de catálogo | EMC Gasket Type  | Treated Edges | Front Finish | Rear Finish | EMC Shielding      | Rack Width |
|--------------------|------------------|---------------|--------------|-------------|--------------------|------------|
| 30846-683          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 84 HP      |
| 30846-771          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 84 HP      |
| 30846-859          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 84 HP      |
| 30846-588          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 84 HP      |
| 30846-864          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 2 HP       |
| 30846-865          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 2 HP       |
| 20846-425          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 3 HP       |
| 20846-426          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 4 HP       |
| 20846-427          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 5 HP       |
| 20846-428          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 6 HP       |
| 20846-429          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 7 HP       |
| 20846-430          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 8 HP       |
| 20846-431          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 10 HP      |
| 20846-432          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 12 HP      |
| 20846-433          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 14 HP      |
| 20846-434          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 21 HP      |
| 20846-436          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 28 HP      |
| 20846-443          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 4 HP       |
| 20846-444          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 5 HP       |
| 20846-445          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 6 HP       |

| Número de catálogo | EMC Gasket Type  | Treated Edges | Front Finish | Rear Finish | EMC Shielding      | Rack Width |
|--------------------|------------------|---------------|--------------|-------------|--------------------|------------|
| 20846-446          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 7 HP       |
| 20846-447          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 8 HP       |
| 20846-448          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 10 HP      |
| 20846-449          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 12 HP      |
| 20846-450          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 14 HP      |
| 20846-451          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 21 HP      |
| 20846-452          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 28 HP      |
| 20846-456          | Acero inoxidable | No            | Anodizado    | Conductive  | No (Retrofittable) | 16 HP      |

| Table 2/3          |                  |          |              |                            |             |          |
|--------------------|------------------|----------|--------------|----------------------------|-------------|----------|
| Número de catálogo | Package Quantity | Altura   | Product Type | Tipo                       | Rack Height | Ancho    |
| 20846-437          | 1                | 128.4 mm | Front Panel  | Front Panel without Handle | 3 U         | 213 mm   |
| 20846-438          | 1                | 128.4 mm | Front Panel  | Front Panel without Handle | 3 U         | 319.7 mm |
| 20846-453          | 1                | 261.8 mm | Front Panel  | Front Panel without Handle | 6 U         | 213 mm   |
| 20846-454          | 1                | 261.8 mm | Front Panel  | Front Panel without Handle | 6 U         | 319.7 mm |
| 30846-676          | 1                | 128.4 mm | Front Panel  | Front Panel without Handle | 3 U         | 426.4 mm |
| 30846-683          | 1                | 172.9 mm | Front Panel  | Front Panel without Handle | 4 U         | 426.4 mm |
| 30846-771          | 1                | 261.8 mm | Front Panel  | Front Panel without Handle | 6 U         | 426.4 mm |
| 30846-859          | 1                | 395.1 mm | Front Panel  | Front Panel without Handle | 9 U         | 426.4 mm |
| 30846-588          | 1                | 84 mm    | Front Panel  | Front Panel without Handle | 2 U         | 426.4 mm |
| 30846-864          | 5                | 128.4 mm | Front Panel  | Front Panel without Handle | 3 U         | 9.8 mm   |

| Número de catálogo | Package Quantity | Altura   | ProductType | Tipo                       | Rack Height | Ancho    |
|--------------------|------------------|----------|-------------|----------------------------|-------------|----------|
| 30846-865          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 9.8 mm   |
| 20846-425          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 14.9 mm  |
| 20846-426          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 20 mm    |
| 20846-427          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 25 mm    |
| 20846-428          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 30.1 mm  |
| 20846-429          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 35.2 mm  |
| 20846-430          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 40.3 mm  |
| 20846-431          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 50.5 mm  |
| 20846-432          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 60.6 mm  |
| 20846-433          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 70.8 mm  |
| 20846-434          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 106.3 mm |
| 20846-436          | 5                | 128.4 mm | Front Panel | Front Panel without Handle | 3 U         | 141.9 mm |
| 20846-443          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 20 mm    |
| 20846-444          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 25 mm    |
| 20846-445          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 30.1 mm  |
| 20846-446          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 35.2 mm  |
| 20846-447          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 40.3 mm  |
| 20846-448          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 50.5 mm  |
| 20846-449          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 60.6 mm  |
| 20846-450          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 70.8 mm  |

| Número de catálogo | Package Quantity | Altura   | ProductType | Tipo                       | Rack Height | Ancho    |
|--------------------|------------------|----------|-------------|----------------------------|-------------|----------|
| 20846-451          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 106.3 mm |
| 20846-452          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 141.9 mm |
| 20846-456          | 5                | 261.8 mm | Front Panel | Front Panel without Handle | 6 U         | 80.9 mm  |

| Table 3/3          |                                 |                |          |
|--------------------|---------------------------------|----------------|----------|
| Número de catálogo | Cumple con                      | Montaje        | Material |
| 20846-437          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-438          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-453          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-454          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 30846-676          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 30846-683          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 30846-771          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 30846-859          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 30846-588          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 30846-864          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 30846-865          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-425          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-426          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-427          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-428          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-429          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |

| Número de catálogo | Cumple con                      | Montaje        | Material |
|--------------------|---------------------------------|----------------|----------|
| 20846-430          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-431          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-432          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-433          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-434          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-436          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-443          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-444          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-445          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-446          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-447          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-448          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-449          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-450          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-451          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-452          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |
| 20846-456          | IEC 60297-3-101, IEEE 1101.1/10 | Screw-on Front | Aluminio |

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

## ADVERTENCIA

---

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



[nVent.com](http://nVent.com)

**TRACER**

Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN RAYCHEM SCHROFF**