

SOCKET STRIP, IEC C13, WITH WIELAND® INPUT



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



CARACTERÍSTICAS

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

ESPECIFICACIONES

Table 1/2

Número de catálogo	Voltage AC	Product Type	Socket Type	Function	Profundidad	Color
60110-340	230 V	Socket Strip	IEC C13		44 mm	Gris
60110-341	230 V	Socket Strip	IEC C13		44 mm	Negro
60110-342	230 V	Socket Strip	IEC C13		44 mm	Rojo
60110-349	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Gris

Número de catálogo	Voltage AC	ProductType	Socket Type	Function	Profundidad	Color
60110-350	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Negro
60110-351	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Rojo

Table 2/2	
Número de catálogo	Longitud
60110-340	438.5 mm
60110-341	438.5 mm
60110-342	438.5 mm
60110-349	438.5 mm
60110-350	438.5 mm
60110-351	438.5 mm

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER