

METAL DE APORTE CADWELD PLUS, F20, 32PLUSF20

CATALOG NUMBER

32PLUSF20



nVent ERICO Cadweld Plus Welding Material, F20, allows for an expedited, permanent grounding connection using pre-measured, self-contained cups. Each package of welding material can be easily placed into the mold and safely ignited with the nVent ERICO Cadweld Plus Impulse Exothermic Welding Control Unit to create an irreversible bond.

CERTIFICATIONS



FEATURES

La mezcla está compuesta principalmente de óxido de cobre y aluminio

Se usa principalmente en aplicaciones de puesta a tierra y unión

Paquete integrado de material de soldadura

Codificación por color según el tamaño para facilitar la identificación

Ignición electrónica

No se requiere material de ignición

No es explosivo

No está sujeto a ignición espontánea

Consulte los detalles específicos de conexión de nVent ERICO Cadweld para determinar los requisitos de materiales de soldadura

ATRIBUTOS DEL PRODUCTO

Article Number: 165702

Anillo codificado por color: Blanco

Cumple con: EN IEC® 62561-1 permanent connection

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

⚠ WARNING: This product can expose you to chemicals including silica, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.