

## FRONT PANEL, UNSHIELDED, WITH FASTENER PIN



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

### CERTIFICATIONS



### CARACTERÍSTICAS

Enable grounding of the front area (protection class 1)

### ESPECIFICACIONES

Table 1/3

| Número de catálogo | Treated Edges | Front Finish | Rear Finish | EMC Shielding | Rack Width | Package Quantity |
|--------------------|---------------|--------------|-------------|---------------|------------|------------------|
| 20119-159          | No            | Anodizado    | Conductive  | No            | 7 HP       | 1                |
| 20119-160          | No            | Anodizado    | Conductive  | No            | 14 HP      | 1                |
| 20119-161          | No            | Anodizado    | Conductive  | No            | 21 HP      | 1                |
| 20119-162          | No            | Anodizado    | Conductive  | No            | 28 HP      | 1                |
| 20119-163          | No            | Anodizado    | Anodizado   | No            | 42 HP      | 1                |

Table 2/3

| Número de catálogo | Altura | Product Type | Tipo | Rack Height | Ancho | Cumple con |
|--------------------|--------|--------------|------|-------------|-------|------------|
|--------------------|--------|--------------|------|-------------|-------|------------|

|           |          |             |                            |     |          |                                 |
|-----------|----------|-------------|----------------------------|-----|----------|---------------------------------|
| 20119-159 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 35.2 mm  | IEC 60297-3-101, IEEE 1101.1/10 |
| 20119-160 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 70.8 mm  | IEC 60297-3-101, IEEE 1101.1/10 |
| 20119-161 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 106.3 mm | IEC 60297-3-101, IEEE 1101.1/10 |
| 20119-162 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 141.9 mm | IEC 60297-3-101, IEEE 1101.1/10 |
| 20119-163 | 128.4 mm | Front Panel | Front Panel without Handle | 3 U | 213 mm   | IEC 60297-3-101, IEEE 1101.1/10 |

Table 3/3

| Número de catálogo | Montaje        | Material |
|--------------------|----------------|----------|
| 20119-159          | Screw-on Front | Aluminio |
| 20119-160          | Screw-on Front | Aluminio |
| 20119-161          | Screw-on Front | Aluminio |
| 20119-162          | Screw-on Front | Aluminio |
| 20119-163          | Screw-on Front | Aluminio |

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**