



# NVENT CADDY SPEED LINK LD LOCKING DEVICE



## FEATURES

Low-profile locking device minimizes visual impact

Suitable for 1.5 mm nVent CADDY Speed Link cable

## SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Material                        | Wire Rope Diameter | Height (H) | Width (W) |
|----------------|----------------|---------------------------------|--------------------|------------|-----------|
| SLJR200        | 196008         | Stainless Steel 304 (EN 1.4301) | 1.5 mm             | 19 mm      | 12.7 mm   |

## ADDITIONAL PRODUCT DETAILS

The 1.5 mm locking devices are only to be used with the SLC15L1000SP and SLC15L50MSP wire spools, or any other 1.5 mm nVent CADDY Speed Link accessories. Do not use with any other wires.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

|                                                                                                     |                                                                                |                                                                                |                                                                                |
|-----------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|--------------------------------------------------------------------------------|--------------------------------------------------------------------------------|
| <b>North America</b><br>+1.800.753.9221<br>Option 1 – Customer Care<br>Option 2 – Technical Support | <b>Europe</b><br>Netherlands:<br>+31 800-0200135<br>France:<br>+33 800 901 793 | <b>Europe</b><br>Germany:<br>800 1890272<br>Other Countries:<br>+31 13 5835404 | <b>APAC</b><br>Shanghai:<br>+ 86 21 2412 1618/19<br>Sydney:<br>+61 2 9751 8500 |
|-----------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|--------------------------------------------------------------------------------|--------------------------------------------------------------------------------|