

RAIL WEB MOLD CLAMP, ADJUSTABLE, T20 WELDER STYLE, 89 MM MOLD SIZE, 600 MM MAX JAW OPENING

CODICE A CATALOGO

PBC105P



CARATTERISTICHE

Adjusts for a wide span of uses including frogs and switches

Lightweight and easy to use

Can also be used on standard (single) rail

SBC105RR provides improved safety with non-sharp profiles and reflecting tape for high visibility

ATTRIBUTI DEL PRODOTTO

Welder Style: T20

Mold Size: 89 mm

Jaw Opening: 600mm max

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER