

CABLE TO WEB OF RAIL MOLD ONLY, POWER, 85-141 LB T-RAIL, 500 KCMIL ROPELAY, LEFT HAND

CODICE A CATALOGO

PBW3SLH



CARATTERISTICHE

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

Connections for power or grounding conductor to the neutral axis

ATTRIBUTI DEL PRODOTTO

Materiale: Graphite

Tipo di rotaia: 85 lb to 141 lb T-Rail Sections

Stile terminale collegamento: W

Dimensioni conduttore: 500 kcmil Ropelay

Diametro esterno conduttore, nominale: 26.42mm

Stile saldatore: T20

Orientamento: Left Hand

Solo stampo: Yes

Materiale per saldatura: PB250, Sold Separately

Handle Clamp: C105C, Sold Separately

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e

degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER