

MSPO PDU, 0U, 60A(48A)NA/63A INT, 380-415V, 3P WYE, 12 CB, (24)C13, (12)C19

CODICE A CATALOGO

EN6908



The Advantage Series Outlet Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at the input phase, circuit breaker, and individual outlet levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

CARATTERISTICHE

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

UL 2900-1 certified for safety software cybersecurity for network-connectable products.

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs

Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

ATTRIBUTI DEL PRODOTTO

Product Family: Enlogic

Type: Intelligent PDU

Product Type: Socket Strip

Socket Type: (24) C13; (12) C19

Socket Quantity: 36

Switched Outlets: Yes

Cable Length: 3000m

Circuit Breaker: 20 A, 1-pole, Hy-MagA

Circuit Breaker Quantity: 12

Current Rating: 43.5kV·A

Nominal Power Output: 230VAC

Nominal Voltage: 415V

Number of Output Voltages: 36

On/Off Switch Included: Yes

Output Voltage: 208 – 230VAC

Plug Type: Dual Rated IEC 60309 560P6/563P6

Rack Units: 0U

Removable Input Cable: No

Metering Type: Outlet

Material: Steel

Finish: Powder Coated

Color: Black

Height: 1750mm

Width: 56mm

Depth: 75mm

Weight: 14kg

Package Quantity: 1

Input Cable Length: 3m

ADDITIONAL PRODUCT DETAILS

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER