

RACKPOWER SINGLE TEMPERATURE AND HUMIDITY SENSOR



Single Temperature and Humidity Probe Sensor for nVent SCHROFF RackPower PDU's.

CARATTERISTICHE

Single Temperature and Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +- 5 %

SPECIFICHE

Table 1/2

Codice a catalogo	Product Type	Famiglia di prodotti	Works With	Quantità per confezione	Altezza	Removable Input Cable
EA9103	Sensor	Enlogic	RackPower	1	270mm	No

Table 2/2

Codice a catalogo	Plug Type
EA9103	RJ45

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER