


SOCKET STRIP, IEC C13



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C13 outlets.

CERTIFICATIONS



CARATTERISTICHE

230 V, 10 A

Horizontal and vertical mounting

Socket strips can be rotated through all four directions (in 90° increments) during installation

Socket strips with IEC 60320-C13 sockets

Connecting cable 2 m, open end with ferrules

In accordance with IEC 60320

Mounting height 1 U

SPECIFICHE

Table 1/2

Codice a catalogo	Product Type	Tipo di presa	Socket Quantity	Switched Outlets	Colore	Tensione AC
60110-290	Socket Strip	IEC C13	8	No	Grey	230V
60110-291	Socket Strip	IEC C13	12	No	Grey	230V
60110-292	Socket Strip	IEC C13	16	No	Grey	230V

Table 2/2

Codice a catalogo	Length	Profondità	Finitura	Materiale	Quantità per confezione
60110-290	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-291	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-292	608.5mm	44mm	Anodized	Aluminum, Polyamide	1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER