

VARISTAR CP BASE/PLINTH

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.



CARATTERISTICHE

2 support profiles, for front and rear

Static load-carrying capacity 1000 kg

SPECIFICHE

Table 1/2

Codice a catalogo	Tipo	Product Type	Altezza	Quantità per confezione	Finitura	Materiale
24630-034	Base Plinth	Cabinet/Rack Base	100mm	1	Powder Coated	Steel
24630-035	Base Plinth	Cabinet/Rack Base	100mm	1	Powder Coated	Steel
24630-036	Base Plinth	Cabinet/Rack Base	200mm	1	Powder Coated	Steel
24630-037	Base Plinth	Cabinet/Rack Base	200mm	1	Powder Coated	Steel
24630-064	Base Plinth	Cabinet/Rack Base	100mm	1	Powder Coated	Steel
24630-065	Base Plinth	Cabinet/Rack Base	100mm	1	Powder Coated	Steel
24630-066	Base Plinth	Cabinet/Rack Base	200mm	1	Powder Coated	Steel
24630-067	Base Plinth	Cabinet/Rack Base	200mm	1	Powder Coated	Steel

Table 2/2

Codice a catalogo	Colore	Codice colore	Larghezza	Profondità
24630-034	Black Grey	RAL 7021	600mm	600mm
24630-035	Black Grey	RAL 7021	800mm	
24630-036	Black Grey	RAL 7021	600mm	
24630-037	Black Grey	RAL 7021	800mm	
24630-064	Black Grey	RAL 7021	600mm	
24630-065	Black Grey	RAL 7021	800mm	
24630-066	Black Grey	RAL 7021	600mm	
24630-067	Black Grey	RAL 7021	800mm	

ADDITIONAL PRODUCT DETAILS

Please order side trims separately.

Cannot be used in conjunction with castors

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER