

VARISTAR CP GLAZED DOOR WITH 3-POINT LOCKING



Glazed door with 3 point locking allows stronger contact between door and the cabinet frame.

CARATTERISTICHE

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICHE

Table 1/3

Codice a catalogo	Tipo	Locking Type	Grado di protezione	È conforme a	Product Type	Altezza
21630-092	Glass Door	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2000mm
21630-093	Glass Door	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2200mm
21630-094	Glass Door	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2450mm
21630-095	Glass Door	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2000mm
21630-096	Glass Door	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2200mm
21630-097	Glass Door	3-Point Locking	IP20	IEC 61587-1, IEC 61587-3	Cabinet Door	2450mm

Table 2/3

Codice a catalogo	Works With	Rack Height	Quantità per confezione	Finitura	Materiale	Colore
21630-092	Varistar CP	42U	1	Powder Coated	Steel, Glass	Black Grey
21630-093	Varistar CP	47U	1	Powder Coated	Steel, Glass	Black Grey
21630-094	Varistar CP	52U	1	Powder Coated	Steel, Glass	Black Grey
21630-095	Varistar CP	42U	1	Powder Coated	Steel, Glass	Black Grey
21630-096	Varistar CP	47U	1	Powder Coated	Steel, Glass	Black Grey
21630-097	Varistar CP	52U	1	Powder Coated	Steel, Glass	Black Grey

Table 3/3

Codice a catalogo	Codice colore	Larghezza
21630-092	RAL 7021	600mm
21630-093	RAL 7021	600mm
21630-094	RAL 7021	600mm
21630-095	RAL 7021	800mm
21630-096	RAL 7021	800mm
21630-097	RAL 7021	800mm

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER