

FRONT PANEL, FRONT ANODIZED, REAR CONDUCTIVE, UNSHIELDED

Front panel, unshielded, front anodized and rear conductive.



CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

SPECIFICATIONS

Table 1/3

Numero catalogo	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30838-123	Nessuno	No	Anodized	Conductive	No	84 HP
30838-204	Nessuno	No	Anodized	Conductive	No	84 HP
30847-465	Nessuno	No	Anodized	Conductive	No	84 HP
30847-469	Nessuno	No	Anodized	Conductive	No	84 HP
30847-461	Nessuno	No	Anodized	Conductive	No	84 HP
30838-081	Nessuno	No	Anodized	Conductive	No	42 HP
30838-102	Nessuno	No	Anodized	Conductive	No	63 HP
30838-162	Nessuno	No	Anodized	Conductive	No	42 HP

Numero catalogo	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30838-183	Nessuno	No	Anodized	Conductive	No	63 HP
30847-459	Nessuno	No	Anodized	Conductive	No	42 HP
30847-460	Nessuno	No	Anodized	Conductive	No	63 HP
30847-463	Nessuno	No	Anodized	Conductive	No	42 HP
30847-464	Nessuno	No	Anodized	Conductive	No	63 HP
30847-467	Nessuno	No	Anodized	Conductive	No	42 HP
30847-468	Nessuno	No	Anodized	Conductive	No	63 HP
30847-458	Nessuno	No	Anodized	Conductive	No	28 HP
30847-470	Nessuno	No	Anodized	Conductive	No	2 HP
30838-067	Nessuno	No	Anodized	Conductive	No	28 HP
30838-043	Nessuno	No	Anodized	Conductive	No	4 HP
30838-044	Nessuno	No	Anodized	Conductive	No	5 HP
30838-045	Nessuno	No	Anodized	Conductive	No	6 HP
30838-046	Nessuno	No	Anodized	Conductive	No	7 HP
30838-047	Nessuno	No	Anodized	Conductive	No	8 HP
30838-049	Nessuno	No	Anodized	Conductive	No	10 HP
30838-051	Nessuno	No	Anodized	Conductive	No	12 HP
30838-053	Nessuno	No	Anodized	Conductive	No	14 HP
30838-055	Nessuno	No	Anodized	Conductive	No	16 HP
30838-060	Nessuno	No	Anodized	Conductive	No	21 HP
30847-471	Nessuno	No	Anodized	Conductive	No	3 HP
30847-476		No	Anodized	Conductive	No	4 HP
30847-462	Nessuno	No	Anodized	Conductive	No	28 HP
30838-124	Nessuno	No	Anodized	Conductive	No	4 HP
30847-466	Nessuno	No	Anodized	Conductive	No	28 HP
30838-125	Nessuno	No	Anodized	Conductive	No	5 HP
30838-126	Nessuno	No	Anodized	Conductive	No	6 HP
30838-127	Nessuno	No	Anodized	Conductive	No	7 HP
30838-128	Nessuno	No	Anodized	Conductive	No	8 HP
30838-130	Nessuno	No	Anodized	Conductive	No	10 HP
30838-132	Nessuno	No	Anodized	Conductive	No	12 HP
30838-134	Nessuno	No	Anodized	Conductive	No	14 HP
30838-136	Nessuno	No	Anodized	Conductive	No	16 HP
30838-141	Nessuno	No	Anodized	Conductive	No	21 HP

Numero catalogo	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30838-148	Nessuno	No	Anodized	Conductive	No	28 HP
30847-480		No	Anodized	Conductive	No	8 HP
30847-482		No	Anodized	Conductive	No	10 HP
30847-484		No	Anodized	Conductive	No	12 HP
30847-556	Nessuno	No	Anodized	Conductive	No	84 HP

Table 2/3						
Numero catalogo	Package Quantity	Altezza	Product Type	Tipo	Rack Height	Larghezza
30838-123	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	426.4 mm
30838-204	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	426.4 mm
30847-465	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	426.4 mm
30847-469	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	426.4 mm
30847-461	1	84 mm	Front Panel	Front Panel without Handle	2 U	426.4 mm
30838-081	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	213 mm
30838-102	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	319.7 mm
30838-162	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	213 mm
30838-183	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	319.7 mm
30847-459	1	84 mm	Front Panel	Front Panel without Handle	2 U	213 mm
30847-460	1	84 mm	Front Panel	Front Panel without Handle	2 U	319.7 mm
30847-463	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	213 mm
30847-464	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	319.7 mm
30847-467	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	213 mm
30847-468	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	319.7 mm

Numero catalogo	Package Quantity	Altezza	ProductType	Tipo	Rack Height	Larghezza
30847-458	5	84 mm	Front Panel	Front Panel without Handle	2 U	141.9 mm
30847-470	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	9.8 mm
30838-067	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	141.9 mm
30838-043	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30838-044	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	25 mm
30838-045	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	30.1 mm
30838-046	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	35.2 mm
30838-047	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	40.3 mm
30838-049	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	50.5 mm
30838-051	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	60.6 mm
30838-053	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	70.8 mm
30838-055		128.4 mm	Front Panel	Front Panel without Handle	3 U	80.9 mm
30838-060	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	106.3 mm
30847-471	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	14.9 mm
30847-476	5	395.1 mm	Front Panel	Front Panel without Handle	4 U	20 mm
30847-462	5	172.9 mm	Front Panel	Front Panel without Handle	4 U	141.9 mm
30838-124	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	20 mm
30847-466	5	217.4 mm	Front Panel	Front Panel without Handle	5 U	141.9 mm
30838-125	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	25 mm
30838-126	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	30.1 mm

Numero catalogo	Package Quantity	Altezza	ProductType	Tipo	Rack Height	Larghezza
30838-127	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	35.2 mm
30838-128	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	40.3 mm
30838-130	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	50.5 mm
30838-132	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	60.6 mm
30838-134	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	70.8 mm
30838-136	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	80.9 mm
30838-141	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	106.3 mm
30838-148	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	141.9 mm
30847-480	5	395.1 mm	Front Panel	Front Panel without Handle	9 U	40.3 mm
30847-482	5	395.1 mm	Front Panel	Front Panel without Handle	9 U	50.5 mm
30847-484	5	395.1 mm	Front Panel	Front Panel without Handle	9 U	60.6 mm
30847-556	5	395.1 mm	Front Panel	Front Panel without Handle	9 U	426.4 mm

Table 3/3				
Numero catalogo	È conforme a	Montaggio	Materiale	Certificazioni
30838-123	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-204	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30847-465	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30847-469	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	
30847-461	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-081	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-102	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS

Numero catalogo	È conforme a	Montaggio	Materiale	Certificazioni
30838-162	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-183	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30847-459	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	
30847-460	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	
30847-463	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30847-464	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30847-467	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	
30847-468	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	
30847-458	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	
30847-470	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-067	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-043	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-044	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-045	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-046	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-047	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-049	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-051	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-053	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-055	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-060	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS

Numero catalogo	È conforme a	Montaggio	Materiale	Certificazioni
30847-471	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30847-476		Screw-on Front	Alluminio	RoHS
30847-462	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	
30838-124	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30847-466	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	
30838-125	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-126	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-127	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-128	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-130	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-132	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-134	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-136	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-141	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30838-148	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS
30847-480		Screw-on Front	Alluminio	RoHS
30847-482		Screw-on Front	Alluminio	RoHS
30847-484		Screw-on Front	Alluminio	RoHS
30847-556	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER