

SOCKET STRIP, SCHUKO, WITH WIELAND® INPUT



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



FEATURES

Installation height 1 U

Output via SCHUKO sockets

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

Horizontal or vertical mounting

In accordance with DIN 57620

SPECIFICATIONS

Table 1/2

Numero catalogo	Voltage AC	Product Type	Socket Type	Function	Profondità	Colore
60110-343	230 V	Socket Strip	SCHUKO		44 mm	Grigio
60110-344	230 V	Socket Strip	SCHUKO		44 mm	Nero
60110-345	230 V	Socket Strip	SCHUKO		44 mm	Rosso
60110-352	230 V	Socket Strip	SCHUKO	Overcurrent Protection	44 mm	Grigio

Numero catalogo	Voltage AC	ProductType	Socket Type	Function	Profondità	Colore
60110-353	230 V	Socket Strip	SCHUKO	Overcurrent Protection	44 mm	Nero
60110-354	230 V	Socket Strip	SCHUKO	Overcurrent Protection	44 mm	Rosso

Table 2/2

Numero catalogo	Lunghezza
60110-343	438.5 mm
60110-344	438.5 mm
60110-345	438.5 mm
60110-352	438.5 mm
60110-353	438.5 mm
60110-354	438.5 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER