

VARISTAR CP GLAZED DOOR WITH 1-POINT LOCKING

FEATURES

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

SPECIFICATIONS

Table 1/3

Numero catalogo	Locking Type	Altezza	Product Type	Product Family	Works With	Tipo
21630-392	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-393	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-481	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-482	Single Point Locking	1200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-394	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-395	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-483	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-484	Single Point Locking	1400 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-396	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-397	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door

Numero catalogo	LockingType	Altezza	ProductType	Product Family	Works With	Tipo
21630-485	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-486	Single Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-398	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-399	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-487	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-488	Single Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-016	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-017	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-489	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-490	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-018	Single Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-019	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-491	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door
21630-492	Single Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Glass Door

Table 2/3						
Numero catalogo	Rack Height	Larghezza	È conforme a	Colore	Materiale	Finitura
21630-392	24 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-393	24 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-481	24 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-482	24 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere

Numero catalogo	Rack Height	Larghezza	È conforme a	Colore	Materiale	Finitura
21630-394	29 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-395	29 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-483	29 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-484	29 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-396	33 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-397	33 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-485	33 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-486	33 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-398	38 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-399	38 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-487	38 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-488	38 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-016	42 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-017	42 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-489	42 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-490	42 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-018	47 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-019	47 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-491	47 U	600 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere
21630-492	47 U	800 mm	IEC 61587-1	Black Grey	Steel, Glass	Verniciato a polvere

Table 3/3

Numero catalogo	Color Code	Protection Rating
21630-392	RAL 7021	IP20
21630-393	RAL 7021	IP20
21630-481	RAL 7021	IP20
21630-482	RAL 7021	IP20
21630-394	RAL 7021	IP20
21630-395	RAL 7021	IP20
21630-483	RAL 7021	IP20
21630-484	RAL 7021	IP20
21630-396	RAL 7021	IP20
21630-397	RAL 7021	IP20
21630-485	RAL 7021	IP20
21630-486	RAL 7021	IP20
21630-398	RAL 7021	IP20
21630-399	RAL 7021	IP20
21630-487	RAL 7021	IP20
21630-488	RAL 7021	IP20
21630-016	RAL 7021	IP20
21630-017	RAL 7021	IP20
21630-489	RAL 7021	IP20
21630-490	RAL 7021	IP20
21630-018	RAL 7021	IP20
21630-019	RAL 7021	IP20
21630-491	RAL 7021	IP20
21630-492	RAL 7021	IP20

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER