

PLUG-IN UNIT KIT WITH IET HANDLE, SHIELDED, BLACK, 6 U



Plug-in unit, with IET inserter/extractor black handle, 3 U, front assembly. The U-shaped front panel enable shielding with a textile gasket.

CERTIFICATIONS



CARATTERISTICHE

U-shaped front panel for textile gasket

Suitable for insertion and extraction forces up to 700 N (per pair)

Enable the installation of a microswitch

Enable the installation of coding pegs in accordance with IEC 60297-3-103/ IEEE 1101.10

SPECIFICHE

Table 1/3

Codice a catalogo	Tipo	Tipo di maniglia	Montaggio	EMC Shielding	EMC Gasket Type	Materiale
20848-766	Front Panel with Handle (PIU)	IET	Screw-on Front	Yes	Textile	Aluminum
20848-767	Front Panel with Handle (PIU)	IET	Screw-on Front	Yes	Textile	Aluminum
20848-768	Front Panel with Handle (PIU)	IET	Screw-on Front	Yes	Textile	Aluminum

Table 2/3

Codice a catalogo	Front Finish	Rear Finish	Treated Edges	Rack Height	Altezza	Rack Width
20848-766	Anodized	Etched	No	6U	261.8mm	4HP
20848-767	Anodized	Etched	No	6U	261.8mm	8HP
20848-768	Anodized	Etched	No	6U	261.8mm	12HP

Table 3/3

Codice a catalogo	Larghezza	È conforme a	Quantità per confezione	Finitura
20848-766	20mm	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	1	Anodized, Passivated
20848-767	40.3mm	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	1	Anodized, Passivated
20848-768	60.6mm	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	1	Anodized, Passivated

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER