

SOCKET STRIP, IEC C13, WITH WIELAND® INPUT



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



FEATURES

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

SPECIFICATIONS

Table 1/2

Numero catalogo	Voltage AC	Product Type	Socket Type	Function	Profondità	Colore
60110-340	230 V	Socket Strip	IEC C13		44 mm	Grigio
60110-341	230 V	Socket Strip	IEC C13		44 mm	Nero
60110-342	230 V	Socket Strip	IEC C13		44 mm	Rosso
60110-349	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Grigio

Numero catalogo	Voltage AC	ProductType	Socket Type	Function	Profondità	Colore
60110-350	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Nero
60110-351	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Rosso

Table 2/2

Numero catalogo	Lunghezza
60110-340	438.5 mm
60110-341	438.5 mm
60110-342	438.5 mm
60110-349	438.5 mm
60110-350	438.5 mm
60110-351	438.5 mm

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER