

RACKPOWER SENSOR INPUT HUB

Sensor Hub to connect 3 sensors on one nVent SCHROFF RackPower PDU Sensor Port.

KENMERKEN

Sensor Hub to connect 3 sensors on one PDU Sensor Port

Black Power coated Housing

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Operating Temperature range 0 to 65 °C

SPECIFICATIES

Table 1/2

Catalogusnummer	Product Type	Productfamilie	Works With	Aantal in verpakking	Hoogte	Removable Input Cable
EA9106	Sensor	Enlogic	RackPower	1	270mm	No

Table 2/2

Catalogusnummer	Plug Type
EA9106	RJ45

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER