

19" FAN UNIT, 1 U, SPEED CONTROL AND MONITORING

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICATIONS



FEATURES

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

SPECIFICATIONS

Table 1/1

Catalogusnummer	Input Voltage DC	Product Type	Input Voltage AC	Accessory Type	Certificeringen
10713-098	24 V min	Fan Unit		Fan unit, 19"	RoHS, CE, EAC
10713-099	24 V min	Fan Unit		Fan unit, 19"	RoHS, CE, EAC
19713-006		Fan Unit	230 V min	Fan unit, 19"	RoHS, EAC
19713-121		Fan Unit	230 V min	Fan unit, 19"	RoHS, EAC

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER