


EUROPACPRO 19" SUBRACK KIT FOR POWER DISTRIBUTION MODULE, UNSHIELDED



For mounting installation devices in accordance with DIN 43880 in sizes 1-3 with snap-in technology e.g. mounting sockets, circuit breakers or residual current circuit breaker. These can be fitted after the horizontal rail with lip DIN central rail (35/7.5) are fitted.

CERTIFICATIONS



FEATURES

For mounting installation devices in accordance with DIN 43880 in sizes 1-3 with snap-in technology e.g. mounting sockets, circuit breakers or residual current circuit breaker. These can be fitted after the horizontal rail with lip DIN central rail (35/7.5) are fitted

Modular frame to accept e.g. power distribution modules

Internal and external dimensions in accordance with the IEC 60297-3-101 and IEEE 1101.1 standards

Aluminium side panels

Horizontal rails type "light"

IEEE 1101.1 compatible

SPECIFICATIONS

Table 1/2

Catalogusnummer	For Mounting	EMC Shielding	Rack Width	Handle Included	Package Quantity	Product Type
24563-100	Power Distribution Module	Nee	84 HP	Nee	1	Subrack/Chassis

Table 2/2

Catalogusnummer	Rack Height	Voldoet aan	Montage	Diepte	Statische belasting
24563-100	3 U	IEC 60297-3-103	Rack	115 mm	2.5 kgf

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:

nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**

TRACER