

GUIDE RAIL WITH CODING, PREASSEMBLED ESD CLIP FOR COMPACTPCI/ VME64X, PC

FEATURES

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to an optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

ESD clip for an conductive contact between PCB and horizontal rail preassembled

Storage temperature: from -40 °C ... 130 °C

SPECIFICATIONS

Table 1/2

Catalogusnummer	Board Depth	Package Quantity	Product Type	Product Family	Works With	Type
24568-847	160 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Sub racks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-848	160 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Sub racks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips

Catalogusnummer	Board Depth	Package Quantity	ProductType	Product Family	Works With	Type
24568-850	160 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-851	160 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-853	70 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-854	70 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-855	70 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-856	70 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips

Table 2/2

Catalogusnummer	Voldoet aan	Kleur	Materiaal	Groove Width
24568-847	EN 45545-2	Rood	Polycarbonaat	2
24568-848	EN 45545-2	Grijs	Polycarbonaat	2
24568-850	EN 45545-2	Rood	Polycarbonaat	2
24568-851	EN 45545-2	Grijs	Polycarbonaat	2
24568-853	EN 45545-2	Rood	Polycarbonaat	2
24568-854	EN 45545-2	Grijs	Polycarbonaat	2
24568-855	EN 45545-2	Rood	Polycarbonaat	2
24568-856	EN 45545-2	Grijs	Polycarbonaat	2

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER