

SECURE DUAL W-LOCK POWER CORD



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

KENMERKEN

Secure dual locking power cords

The IEC C14/C20 plug will lock into any RackPower PDU

The universal locking IEC connector will securely lock into any standard C14/C20 power inlet

Both connections require deliberate action in order to release the locking buttons and disconnect power

SPECIFICATIES

Table 1/2

Catalogusnummer	Product Type	Productfamilie	Works With	Lengte	Type	Aantal in verpakking
EP1314024X150	Cable	Enlogic	RackPower	600mm	Cable	150
EP1314048X125	Cable	Enlogic	RackPower	1200mm	Cable	125
EP1314072X100	Cable	Enlogic	RackPower	1800mm	Cable	100
EP1314B24X150	Cable	Enlogic	RackPower	600mm	Cable	150
EP1314B48X125	Cable	Enlogic	RackPower	1200mm	Cable	125
EP1314B72X100	Cable	Enlogic	RackPower	1800mm	Cable	100
EP1314R24X150	Cable	Enlogic	RackPower	600mm	Cable	150
EP1314R48X125	Cable	Enlogic	RackPower	1200mm	Cable	125
EP1314R72X100	Cable	Enlogic	RackPower	1800mm	Cable	100
EP1920024X100	Cable	Enlogic	RackPower	600mm	Cable	100

Catalogusnummer	ProductType	Productfamilie	Works With	Lengte	Type	Aantal in verpakking
EP1920048X75	Cable	Enlogic	RackPower	1200mm	Cable	75
EP1920072X50	Cable	Enlogic	RackPower	1800mm	Cable	50
EP1920B24X100	Cable	Enlogic	RackPower	600mm	Cable	100
EP1920B48X75	Cable	Enlogic	RackPower	1200mm	Cable	75
EP1920B72X50	Cable	Enlogic	RackPower	1800mm	Cable	50
EP1920R24X100	Cable	Enlogic	RackPower	600mm	Cable	100
EP1920R48X75	Cable	Enlogic	RackPower	1200mm	Cable	75
EP1920R72X50	Cable	Enlogic	RackPower	1800mm	Cable	50

Table 2/2

Catalogusnummer	Kleur	Hoogte	Removable Input Cable	Plug Type	Input Cable Length
EP1314024X150	Black	270mm	No	C13/C14	588m
EP1314048X125	Black	270mm	No	C13/C14	1.176m
EP1314072X100	Black	270mm	No	C13/C14	1.764m
EP1314B24X150	Blue	270mm	No	C13/C14	0.588m
EP1314B48X125	Blue	270mm	No	C13/C14	1.176m
EP1314B72X100	Blue	270mm	No	C13/C14	1.764m
EP1314R24X150	Red	270mm	No	C13/C14	0.588m
EP1314R48X125	Red	270mm	No	C13/C14	1.176m
EP1314R72X100	Red	270mm	No	C13/C14	1.764m
EP1920024X100	Black	270mm	No	C19/C20	0.588m
EP1920048X75	Black	270mm	No	C19/C20	1.176m
EP1920072X50	Black	270mm	No	C19/C20	1.764m
EP1920B24X100	Blue	270mm	No	C19/C20	0.588m
EP1920B48X75	Blue	270mm	No	C19/C20	1.176m
EP1920B72X50	Blue	270mm	No	C19/C20	1.764m
EP1920R24X100	Red	270mm	No	C19/C20	0.588m
EP1920R48X75	Red	270mm	No	C19/C20	1.176m
EP1920R72X50	Red	270mm	No	C19/C20	1.764m

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan

leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER