

TD COMPACT FOUR POLE DISTRIBUTION BLOCK, 40 A



CERTIFICATIONS



KENMERKEN

Minimum space for maximum power

Protection cover and insulating screens are transparent

Insulating screen between each row

Easy and safe connections

Easily clips onto DIN rail or mounts to panel with screws

Solid bars provide reliability

Wiring with or without terminal

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free

SPECIFICATIES

Table 1/4

Catalogusnummer	Article Number	Max Current Rating, IEC	Peak Short Circuit Current (I _{pk})	Line Side Stranded Wire Size - Ferrule	Line Side Compact Stranded Wire Size	Materiaal
TD-40A	563740	40A	22kA	4 – 10mm ²	6 - 16 mm ²	Thermoplastic, Brass

Table 2/4

Catalogusnummer	Article Number	Short Term Withstand Current (I _{cw}) 1s	Line Side Number of Connections	Load Side Number of Connections	Load Side Compact Stranded Wire Size	Load Side Stranded Wire Size - Ferrule
TD-40A	563740	4.5kA	2	11	(11) 1,5 - 4 mm ²	(11) 0,75 – 4 mm ²

Table 3/4

Catalogusnummer	Article Number	Max Working Voltage, IEC (U _i)	Hoogte (H)	Breedte (W)	Diepte (D)	Eenheid gewicht (metrisch)
TD-40A	563740	500	90mm	100mm	50mm	0.33kg

Table 4/4


Catalogusnummer	Article Number	Flammability Rating	Conform
TD-40A	563740	UL® 94V-0	IEC® 60947-7-1

ADDITIONAL PRODUCT DETAILS

Line side and load side number of connections are per pole.

Design Guideline for Distribution Blocks, Power Blocks and Power Terminals										
Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C										
Ambient Temperature (°C)	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°
Derating Coefficient (d)	1	1	1	0.94	0.88	0.82	0.75	0.67	0.58	0.47
*environment around the terminal blocks inside the enclosure										

DIAGRAMS



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER