

## CRIMPING COMPRESSION TOOL DIE, TYPE ML, HEAVY-DUTY DIN46235, 120 MM<sup>2</sup> STRANDED, 250 KCMIL STRANDED

### NUMER KATALOGOWY

**PKML120**



### KENMERKEN

Suitable for cable lugs and connectors

### ATRYBUTY PRODUKTU

Article Number: 716996

Typ występu/złącza: Heavy-Duty DIN46235

Rozmiar przewodnika: 120 mm<sup>2</sup> Stranded; 250 kcmil Stranded

Szerokość zaciskania: 5mm

Tool: MLB

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**