

RACKPOWER SINGLE TEMPERATURE AND HUMIDITY SENSOR



Single Temperature and Humidity Probe Sensor for nVent SCHROFF RackPower PDU's.

KENMERKEN

Single Temperature and Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +- 5 %

SPECYFIKACJE

Table 1/2

Numer katalogowy	Product Type	Rodzina produktów	Works With	Ilość w opakowaniu	Wysokość	Removable Input Cable
EA9103	Sensor	Enlogic	RackPower	1	270mm	No

Table 2/2

Numer katalogowy	Plug Type
EA9103	RJ45

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER