

SOCKET STRIP, IEC C13, METERED

PDU with local power meter. Relevant Power data are shown on an integrated display.



CERTIFICATIONS



KENMERKEN

Socket strips can be rotated through all four directions (in 90° increments) during installation

Mounting height 1 U

Integrated measurement and display via local display unit

Socket strips with IEC 60320-C13 sockets

Horizontal and vertical mounting

SPECYFIKACJE

Table 1/2

Numer katalogowy	Product Type	Typ gniazda	Socket Quantity	Switched Outlets	Kolor	Napięcie AC
60110-296	Socket Strip	IEC C13	8	Yes	Grey	230V

Table 2/2

Numer katalogowy	Length	Głębokość	Materiał	Ilość w opakowaniu
60110-296	438.5mm	44mm	Aluminum, Polyamide	1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER