

19" FAN UNIT, 1 U, REMOTE CONTROL AND MONITORING

Fan Unit with ModBus interface for installation into a 1 U space within the Cabinet

CARACTERÍSTICAS

Fan speed temperature controlled

ModBus Interface for Remote Monitoring and Control

Temperature threshold for the fan control adjustable on the front panel

Signaling of fan failure and over temperature by 2 LEDs and potential-free relay outputs

Integrated power supply with wide range input (100 V – 240 V)

Less than 1 U (42 mm) to enable mounting on sliding guide rails or drawer

2 NTC temperature sensors with Cables included

SPECIFICATIONS

Table 1/2

Número do catálogo	Airflow	Noise Level	Alimentação	Max Static Pressure	Ambient Temperature	Lifespan, L10 @ 40 C
10713-554	1089 m³/h	59.5 dB(A)	97 W	78 Pa	-10 to 70 °C	99558 h

Table 2/2

Número do catálogo	Product Type	Input Voltage AC
10713-554	Fan Unit	100 – 240 V

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER