

MONITOR, KEYBOARD, TOUCHPAD, 1 U DRAWER



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICATIONS



CARACTERÍSTICAS

Pull-out 17" TFT color monitor chassis, 1 U (resolution 1280 x 1024; connects to VGA interface)

Keyboard with different language keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 470 ... 740 mm

ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Product Type	Tipo	Works With	Cor	Código de cor	Rack Height
60118-580	Cabinet/Rack Drawer	Monitor, Keyboard, Touchpad	19" Cabinets	Jet Black	RAL 9005	1U
60118-581	Cabinet/Rack Drawer	Monitor, Keyboard, Touchpad	19" Cabinets	Jet Black	RAL 9005	1U

Número de catálogo	ProductType	Tipo	Works With	Cor	Código decor	Rack Height
60118-582	Cabinet/Rack Drawer	Monitor, Keyboard, Touchpad	19" Cabinets	Jet Black	RAL 9005	1U

Table 2/2

Número de catálogo	Profundidade	Quantidade por embalagem
60118-580	470mm	1
60118-581	470mm	1
60118-582	470mm	1

ADDITIONAL PRODUCT DETAILS

Further versions on request. With trackball or numeric pad.

Other Keyboard layouts see user manual.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER