

SOCKET STRIP, IEC C13, WITH WIELAND® INPUT



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



CARACTERÍSTICAS

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

SPECIFICATIONS

Table 1/2

Número do catálogo	Voltage AC	Product Type	Socket Type	Function	Profundidade	Cor
60110-340	230 V	Socket Strip	IEC C13		44 mm	Grey
60110-341	230 V	Socket Strip	IEC C13		44 mm	Preto
60110-342	230 V	Socket Strip	IEC C13		44 mm	Vermelho
60110-349	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Grey

Número do catálogo	Voltage AC	ProductType	Socket Type	Function	Profundidade	Cor
60110-350	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Preto
60110-351	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Vermelho

Table 2/2

Número do catálogo	Comprimento
60110-340	438.5 mm
60110-341	438.5 mm
60110-342	438.5 mm
60110-349	438.5 mm
60110-350	438.5 mm
60110-351	438.5 mm

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER