

RACKPOWER SENSOR INPUT HUB

Sensor Hub to connect 3 sensors on one nVent SCHROFF RackPower PDU Sensor Port.

CARACTERISTICI

Sensor Hub to connect 3 sensors on one PDU Sensor Port

Black Power coated Housing

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Operating Temperature range 0 to 65 °C

SPECIFICAȚII

Table 1/2

Număr de catalog	Product Type	Product Family	Works With	Package Quantity	Height	Removable Input Cable
EA9106	Sensor	Enlogic	RackPower	1	270mm	No

Table 2/2

Număr de catalog	Plug Type
EA9106	RJ45

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER