

ПАНЕЛЬ ЭЛЕКТРОПИТАНИЯ, IEC C13, С ВХОДОМ WIELAND®



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Эта панель электропитания с алюминиевым шасси размером 1 U x 1 U легко интегрируется в шкаф. Разъем Wieland обеспечивает простую комбинацию с различными входными кабелями питания.

CERTIFICATIONS



FEATURES

Вход: штекер Wieland® GST 18

Установочная высота 1 U

В соответствии с IEC 60320

Горизонтальная или вертикальная установка

Выходы: розетки IEC 60320 C-13

Во время установки панель электропитания можно поворачивать во всех направлениях (с шагом 90°)

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-340	Socket Strip	IEC C13	12	No	Grey	230V
60110-341	Socket Strip	IEC C13	12	No	Black	230V
60110-342	Socket Strip	IEC C13	12	No	Red	230V
60110-349	Socket Strip	IEC C13	6	No	Grey	230V

Catalog Number	ProductType	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-350	Socket Strip	IEC C13	6	No	Black	230V
60110-351	Socket Strip	IEC C13	6	No	Red	230V

Table 2/2						
Catalog Number	Function	Длина мм	Глубина мм	Material	Finish	Package Quantity
60110-340		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-341		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-342		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-349	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-350	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-351	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1

ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER