

## RACKPOWER 3X TEMPERATURE AND 1X HUMIDITY SENSOR



3x Temperature and 1x Humidity Probe Sensor for nVent SCHROFF RackPower PDU's.

### FEATURES

3x Temperature and 1x Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +- 5 %

Second and Third Temperature Sensor with 950 mm cable

### SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Product Family	Works With	Package Quantity	Высота мм	Removable Input Cable
EA9105	Sensor	Enlogic	RackPower	1	270mm	No

Table 2/2

Catalog Number	Plug Type
EA9105	RJ45

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**