

GUIDE RAIL WITH CODING FOR COMPACTPCI/ VME64X, ПОЛИКАРБОНАТ



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

CERTIFICATIONS



FEATURES

НОВОЕ поколение с пластмассовыми направляющими кодирующего типа для надежной фиксации печатных плат или вставных блоков

Значительно повышенная устойчивость, благодаря оптимизированной конструкции и высококачественному материалу (поликарбонат)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

«Не содержат галогенов», согласно IEC 61249-2-21

Могут быть закреплены на горизонтальных рельсах (алюминиевый экструдированный профиль) или на панелях толщиной 1,5 мм

Для более высоких требований в отношении ударных нагрузок и вибрации направляющие могут прикручиваться болтами к горизонтальной рейке (тип H и тип R)

Доступен дополнительный зажим ESD для проводящего контакта между печатной платой и горизонтальным рельсом

Температура хранения: от -40 °C до 130 °C

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Works With	Board Depth	Material	Color	Package Quantity
----------------	------	------------	-------------	----------	-------	------------------

64568-089	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic	Red	1
64568-090	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic	Grey	1
64568-085	Coding	Subracks, Cases, 19" Chassis, Systems	70mm	Fiber-Reinforced Plastic	Red	1
64568-086	Coding	Subracks, Cases, 19" Chassis, Systems	70mm	Fiber-Reinforced Plastic	Grey	1
64568-091	Coding	Subracks, Cases, 19" Chassis, Systems	220mm	Fiber-Reinforced Plastic	Red	1
64568-092	Coding	Subracks, Cases, 19" Chassis, Systems	220mm	Fiber-Reinforced Plastic	Grey	1
64568-111	Coding	Subracks, Cases, 19" Chassis, Systems	220mm	Fiber-Reinforced Plastic, Aluminum	Red, Silver	1
64568-109	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic, Aluminum	Red, Silver	1
64568-110	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	1
64568-112	Coding	Subracks, Cases, 19" Chassis, Systems	220mm	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	1
24568-356	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic	Red	10
24568-357	Coding	Subracks, Cases, 19" Chassis, Systems	70mm	Fiber-Reinforced Plastic	Red	10

24568-358	Coding	Subracks, Cases, 19" Chassis, Systems	160mm	Fiber-Reinforced Plastic	Grey	10
24568-360	Coding	Subracks, Cases, 19" Chassis, Systems	70mm	Fiber-Reinforced Plastic	Grey	10
24568-331	Coding	Subracks, Cases, 19" Chassis, Systems	280mm	Fiber-Reinforced Plastic, Aluminum	Red, Silver	10
24568-332	Coding	Subracks, Cases, 19" Chassis, Systems	340mm	Fiber-Reinforced Plastic, Aluminum	Red, Silver	10
24568-341	Coding	Subracks, Cases, 19" Chassis, Systems	280mm	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	10
24568-342	Coding	Subracks, Cases, 19" Chassis, Systems	340mm	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	10

Table 2/2

Catalog Number	Complies With	Groove Width	Finish
64568-089	EN 45545-2	2	
64568-090	EN 45545-2	2	
64568-085	EN 45545-2	2	
64568-086	EN 45545-2	2	
64568-091	EN 45545-2	2	
64568-092	EN 45545-2	2	
64568-111	EN 45545-2	2.5	
64568-109	EN 45545-2	2.5	
64568-110	EN 45545-2	2.5	
64568-112	EN 45545-2	2.5	
24568-356	EN 45545-2	2	
24568-357	EN 45545-2	2	
24568-358	EN 45545-2	2	
24568-360	EN 45545-2	2	
24568-331	EN 45545-2	2.5	Anodized

Catalog Number	Complies With	Groove Width	Finish
24568-332	EN 45545-2	2.5	Anodized
24568-341	EN 45545-2	2.5	Anodized
24568-342	EN 45545-2	2.5	

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER