

BRANCH LINE RESTRAINT STRUCTURE ATTACHMENT TO THREADED HOLE



CERTIFICATIONS



DESIGN

Swivel barrel nut accepts 3/8" or 1/2" (M10 or M12) threaded rod

Attaches to concrete anchors or structural attachments with female threads

Can be used for bolting through steel

SPECIFIKATIONER

Table 1/2

Katalognummer	Article Number	Material	Finish	Längd (L)	Gångstorlek (RS)	Skruvdiameter (Sc)
CSBBRS3MEG	402241	Steel	Electrogalvanized	40.4mm	10, 12	10


Table 2/2

Katalognummer	Article Number	Höjd (H)	Skruvlängd (L)	Bredd (W)
CSBBRS3MEG	402241	28.2mm	19mm	26.9mm

ADDITIONAL PRODUCT DETAILS

Branch line structural attachments are for restraint only and not for the hanging of fire sprinkler piping.

DIAGRAMS



VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER