

SKÅRADE FRONTPANELER | KRAFTDISTRIBUTION, MSMCP



This mild steel slotted front panel, MSMCP, is for the front frame of a fix system, or modular frames. No machining is required when it is used for mounting modular components.

DESIGN

Beskrivning: Skårad frontpanel för modulenheter. Levereras med en DIN-skena per rad för modulkomponenter. Böjd upptill och nedtill för att ge extra styvhet.

Material: 1.25 mm stål.

Ytbehandling: Pulverlack RAL 7035 med strukturerad yta.

Leverans: 1 styck med monteringsmaterial.

Erforderliga tillbehör: Monteras på modulsystemramen.

The panels are to be mounted onto a fix system front frame (MSFCP) or onto modular system frames (MSMSF or MSMSM)

Slotted front panel for modular assemblies

Provided with one DIN rail per row for modular components

It has a top and bottom bending to provide extra rigidity

One piece with mounting material

To be assembled on the modular system frame

SPECIFIKATIONER

Tjocklek:	1.25mm
Färg:	Ljusgrå
Material:	Mild Steel
Finish:	Pulverlackerad strukturerad yta
Färgkod:	Ral 7035

Table 1/1

Katalognummer	E-Number	Höjd	Bredd	Djup	Elektrodlängd	Produktfamilj
MSMCP1506R5	2504634	150mm	600mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP1508R5	2504640	150mm	800mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP2006R5	2504635	200mm	600mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP2008R5	2504641	200mm	800mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP3006-1R5	2504636	300mm	600mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP3006-2R5		300mm	800mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP3008-1R5		300mm	600mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP3008-2R5		300mm	800mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP4506R5	2504638	450mm	600mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP4508R5	2504643	450mm	800mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP6006R5	2504639	600mm	600mm	13mm	Mild Steel	Free-Standing, Wall Mounted
MSMCP6008R5	2504644	600mm	800mm	13mm	Mild Steel	Free-Standing, Wall Mounted

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER