

T-SERIENS LUFTKONDITIONERING FÖR UTOMHUSBRUK



T-Series Compact Outdoor Air Conditioners provide a compact footprint to minimize real estate and maximize capacity. Their discreet design helps them to blend into rugged factory or outdoor environments. Each unit is equipped with corrosion-resistant components, compressor heaters and head pressure controls for optimal outdoor performance.

BRANSCHSTANDARDER

UL/cUL Listed; Type 12, 3R, 4; 4X optional; File No. SA6453

UR/cUR Recognized

UR/cUR Recognized on select models, reference performance data tables.

CE

EAC

Telcordia GR-487 capable

DESIGN

Compact footprint to minimize real estate and maximize capacity

Models for 115, 230 and 460 VAC power input

Outdoor model operating temperature range from -40 F/-40 C to 131 F/55 C

UL Listed to save customers time and money with agency approvals (some models UL recognized)

Painted galvanized or stainless steel sheet-metal cover for rugged factory and outdoor environments

Reliable mechanical thermostat on enclosure side of the unit

Dual condenser-side air movers for performance redundancy

Cleanable, reusable aluminum mesh filter protects coils for maximum cooling performance

Exterior and fully recessed mounting options on many models

Easy-mount flanges for simple installation

Every unit functionally tested before shipping

Standard Outdoor Air Conditioner models include: Thermostat, corrosion-resistant components, malfunction switch, compressor heater, head pressure control, enclosure heater and R134A refrigerant

Monteringshårdvara, packningar och användarmanual medföljer enheten

Item T150116G120 is only for indoor purpose

SPECIFIKATIONER

Tjocklek: 1.21mm

Färg: Ljusgrå

Färgkod: Ral 7035

Table 1/1

Katalognummer	Nominell kapacitet Btu/h	Nominell kapacitet Watt	Nominell spänning	Antal faser	Material	Finish
T150116G120	800Btu/h	235W	115V	1	Mild Steel	Pulverlackerad strukturerad yta
T150116G152	800Btu/h	235W	115V	1	Rostfritt stål 304	Brushed #3
T150116G100	800Btu/h	235W	115V	1	Mild Steel	Pulverlackerad strukturerad yta
T150116G150	800Btu/h	235W	115V	1	Mild Steel	Pulverlackerad strukturerad yta
T150116G151	800Btu/h	235W	115V	1	Rostfritt stål 304	Brushed #3
T150126G100	900Btu/h	264W	230V	1	Mild Steel	Pulverlackerad strukturerad yta
T150126G104	900Btu/h	264W	230V	1	Rostfritt stål 304	Brushed #3
T150126G120	900Btu/h	264W	230V	1	Mild Steel	Pulverlackerad strukturerad yta
T150126G150	900Btu/h	264W	230V	1	Mild Steel	Pulverlackerad strukturerad yta
T200216G100	2000Btu/h	586W	115V	1	Mild Steel	Pulverlackerad strukturerad yta
T200216G150	2000Btu/h	586W	115V	1	Mild Steel	Pulverlackerad strukturerad yta
T200216G155	2000Btu/h	586W	115V	1	Rostfritt stål 304	Brushed #3
T200216G157	2000Btu/h	586W	115V	1	Rostfritt stål 304	Brushed #3
T200226G100	2000Btu/h	586W	230V	1	Mild Steel	Pulverlackerad strukturerad yta
T200226G103	2000Btu/h	586W	230V	1	Rostfritt stål 304	Brushed #3
T200226G150	2000Btu/h	586W	230V	1	Mild Steel	Pulverlackerad strukturerad yta
T200226G158	2000Btu/h	586W	230V	1	Rostfritt stål 304	Brushed #3
T200246G400	2000Btu/h	586W	460V	1	Mild Steel	Pulverlackerad strukturerad yta
T200246G401	2000Btu/h	586W	460V	1	Rostfritt stål 304	Brushed #3
T290416G150	4000Btu/h	1172W	115V	1	Mild Steel	Pulverlackerad strukturerad yta
T290416G159	4000Btu/h	1172W	115V	1	Rostfritt stål 304	Brushed #3
T430616G102	6303Btu/h	1846W	115V	1	Rostfritt stål 304	Brushed #3

Katalognummer	Nominell kapacitet Btu/h	Nominell kapacitet Watt	Nominell spänning	Antal faser	Material	Finish
T430616G150	6303Btu/h	1846W	115V	1	Mild Steel	Pulverlackerad strukturerad yta
T430816G150	8100Btu/h	2374W	115V	1	Mild Steel	Pulverlackerad strukturerad yta
T430816G153	8100Btu/h	2374W	115V	1	Rostfritt stål 304	Brushed #3
T430826G108	8200Btu/h	2403W	230V	1	Rostfritt stål 304	Brushed #3
T431016G102	11000Btu/h	3224W	115V	1	Rostfritt stål 304	Brushed #3
T431016G150	11000Btu/h	3224W	115V	1	Mild Steel	Pulverlackerad strukturerad yta
T431026G104	10200Btu/h	2989W	230V	1	Rostfritt stål 304	Brushed #3
T290426G150	4000Btu/h	1172W	230V	1	Mild Steel	Pulverlackerad strukturerad yta
T290426G161	4000Btu/h	1172W	230V	1	Rostfritt stål 304	Brushed #3
T430626G150	6600Btu/h	1934W	230V	1	Mild Steel	Pulverlackerad strukturerad yta
T430626G159	6600Btu/h	1934W	230V	1	Rostfritt stål 304	Brushed #3
T430826G150	8200Btu/h	2403W	230V	1	Mild Steel	Pulverlackerad strukturerad yta
T501226G125	12407Btu/h	3636W	230V	1	Rostfritt stål 304	Brushed #3
T501226G150	12407Btu/h	3636W	230V	1	Mild Steel	Pulverlackerad strukturerad yta
T531926G109	20400Btu/h	5978W	230V	1	Rostfritt stål 304	Brushed #3

ADDITIONAL PRODUCT DETAILS

*Reference the Spec Sheet for complete product specifications, performance curves and detailed drawings

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER