

FRONT PANEL, REFROFIT SHIELDING



Flat front panel. Shieldable with stainless steel EMC gasket.

CERTIFICATIONS



FEATURES

For stainless steel EMC gasket

Aluminum, 2.5 mm, front anodized, conductive

SPECIFICATIONS

Table 1/3

Katalognummer	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
20846-437	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	42 HP
20846-438	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	63 HP
20846-453	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	42 HP
20846-454	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	63 HP
30846-676	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	84 HP

Katalognummer	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30846-683	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	84 HP
30846-771	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	84 HP
30846-859	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	84 HP
30846-588	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	84 HP
30846-864	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	2 HP
30846-865	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	2 HP
20846-424	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	16 HP
20846-425	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	3 HP
20846-426	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	4 HP
20846-427	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	5 HP
20846-428	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	6 HP
20846-429	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	7 HP
20846-430	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	8 HP
20846-431	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	10 HP
20846-432	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	12 HP
20846-433	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	14 HP
20846-434	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	21 HP
20846-436	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	28 HP
20846-442	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	3 HP
20846-443	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	4 HP

Katalognummer	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
20846-444	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	5 HP
20846-445	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	6 HP
20846-446	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	7 HP
20846-447	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	8 HP
20846-448	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	10 HP
20846-449	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	12 HP
20846-450	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	14 HP
20846-451	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	21 HP
20846-452	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	28 HP
20846-456	Rostfritt stål	Nej	Anodized	Conductive	No (Retrofittable)	16 HP

Table 2/3						
Katalognummer	Package Quantity	Höjd	Product Type	Typ	Rack Height	Bredd
20846-437	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	213 mm
20846-438	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	319.7 mm
20846-453	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	213 mm
20846-454	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	319.7 mm
30846-676	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	426.4 mm
30846-683	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	426.4 mm
30846-771	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	426.4 mm
30846-859	1	395.1 mm	Front Panel	Front Panel without Handle	9 U	426.4 mm

Katalognummer	Package Quantity	Höjd	ProductType	Typ	Rack Height	Bredd
30846-588	1	84 mm	Front Panel	Front Panel without Handle	2 U	426.4 mm
30846-864	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	9.8 mm
30846-865	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	9.8 mm
20846-424		128.4 mm	Front Panel	Front Panel without Handle	3 U	80.9 mm
20846-425	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	14.9 mm
20846-426	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
20846-427	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	25 mm
20846-428	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	30.1 mm
20846-429	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	35.2 mm
20846-430	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	40.3 mm
20846-431	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	50.5 mm
20846-432	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	60.6 mm
20846-433	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	70.8 mm
20846-434	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	106.3 mm
20846-436	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	141.9 mm
20846-442		261.8 mm	Front Panel	Front Panel without Handle	6 U	14.9 mm
20846-443	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	20 mm
20846-444	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	25 mm
20846-445	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	30.1 mm
20846-446	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	35.2 mm

Katalognummer	Package Quantity	Höjd	ProductType	Typ	Rack Height	Bredd
20846-447	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	40.3 mm
20846-448	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	50.5 mm
20846-449	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	60.6 mm
20846-450	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	70.8 mm
20846-451	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	106.3 mm
20846-452	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	141.9 mm
20846-456	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	80.9 mm

Table 3/3			
Katalognummer	Uppfyller kraven enligt	Montering	Material
20846-437	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-438	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-453	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-454	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30846-676	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30846-683	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30846-771	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30846-859	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30846-588	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30846-864	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30846-865	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-424	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium

Katalognummer	Uppfyller kraven enligt	Montering	Material
20846-425	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-426	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-427	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-428	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-429	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-430	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-431	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-432	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-433	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-434	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-436	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-442	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-443	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-444	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-445	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-446	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-447	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-448	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-449	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-450	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-451	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium

Katalognummer	Uppfyller kraven enligt	Montering	Material
20846-452	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
20846-456	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER