

## SOCKET STRIP, IEC C13



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C13 outlets.

### CERTIFICATIONS



### DESIGN

230 V, 10 A

Horizontal and vertical mounting

Socket strips can be rotated through all four directions (in 90° increments) during installation

Socket strips with IEC 60320-C13 sockets

Connecting cable 2 m, open end with ferrules

In accordance with IEC 60320

Mounting height 1 U

### SPECIFIKATIONER

Table 1/2

| Katalognummer | Product Type | Uttagstyp | Socket Quantity | Switched Outlets | Färg | Spänning AC |
|---------------|--------------|-----------|-----------------|------------------|------|-------------|
| 60110-290     | Socket Strip | IEC C13   | 8               | No               | Grey | 230V        |
| 60110-291     | Socket Strip | IEC C13   | 12              | No               | Grey | 230V        |
| 60110-292     | Socket Strip | IEC C13   | 16              | No               | Grey | 230V        |

Table 2/2

| Katalognummer | Length  | Djup | Material            | Finish   | Förpackningsmängd |
|---------------|---------|------|---------------------|----------|-------------------|
| 60110-290     | 438.5mm | 44mm | Aluminum, Polyamide | Anodized | 1                 |
| 60110-291     | 438.5mm | 44mm | Aluminum, Polyamide | Anodized | 1                 |
| 60110-292     | 608.5mm | 44mm | Aluminum, Polyamide | Anodized | 1                 |

## ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

## VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)



Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**