

## BASIC PDU, EB0811, 400 VAC, 3-PH, 32 A

### 目录编号

**EB0811**



Modular, compact PDU. Ultra-Low Profile Design

### 功能

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

### 产品属性

Produkttyp: Steckdosenleiste

Steckdosentyp: (30) C13; (12) C19

Anzahl Buchsen: 42

Farben: Schwarz

Geschaltete Ausgänge: Nein

Leitungsschutzschalter: 16 A, 1-pole, Hy-Mag

Menge Leistungsschalter: 6

Strombelastbarkeit: 22A

Oberfläche: Pulverbeschichtung

Höhe: 1750mm

Länge des Eingangskabels: 3m

Position des Eingangskabels: Top Feed

Eingangsstrom: 32 A

Eingangsspannung: 380-415 VAC, 3 PH

Maximale Leistungsaufnahme: 22.0 kVA

Metering Type: Keine

Nennspannung: 415V

Ein-/Ausschalter im Lieferumfang enthalten: Nein

Ausgangsspannung: 230VAC

Packungsmenge: 1

Stecker-Typ: IEC 60309 532P6 (IP44)

Produktfamilie: Enlogic

Rack Units: 0U

Removable Input Cable: Nein

Typ: Basic PDU

## ADDITIONAL PRODUCT DETAILS

---

Please order bracket for vertical mounting separately.

## 警告

---

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:  
[nVent.com](https://www.nVent.com) CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.