

VARISTAR CP PERFORATED DOOR, SEISMIC IP20, MULTI-POINT LOCKING

IP 20 抗震门，带已加固的多点锁定。

多点锁定有助于实现必要的接触，以免电子设备受到 EMI 影响。

功能

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

带按钮的摇柄锁

SPECIFICATIONS

Table 1/3

物料号	锁定类型	高度	产品类型	产品系列	搭配使用	类型
21630-876	4-Point Locking	1600 mm	机柜门	Varistar CP	Varistar CP	Steel Door, Perforated
21630-877	4-Point Locking	1600 mm	机柜门	Varistar CP	Varistar CP	Steel Door, Perforated
21630-878	4-Point Locking	1800 mm	机柜门	Varistar CP	Varistar CP	Steel Door, Perforated
21630-879	4-Point Locking	1800 mm	机柜门	Varistar CP	Varistar CP	Steel Door, Perforated
21630-880	4-Point Locking	2000 mm	机柜门	Varistar CP	Varistar CP	Steel Door, Perforated
21630-881	4-Point Locking	2000 mm	机柜门	Varistar CP	Varistar CP	Steel Door, Perforated
21630-882	5-Point Locking	2200 mm	机柜门	Varistar CP	Varistar CP	Steel Door, Perforated
21630-883	5-Point Locking	2200 mm	机柜门	Varistar CP	Varistar CP	Steel Door, Perforated

Table 2/3						
物料号	机架高度	宽度	符合	颜色	材料	色号
21630-876	33 U	600 mm	IEC 61587-1, IEC 61587-2	暗灰色	钢	RAL 7021
21630-877	33 U	800 mm	IEC 61587-1, IEC 61587-2	暗灰色	钢	RAL 7021
21630-878	38 U	600 mm	IEC 61587-1, IEC 61587-2	暗灰色	钢	RAL 7021
21630-879	38 U	800 mm	IEC 61587-1, IEC 61587-2	暗灰色	钢	RAL 7021
21630-880	42 U	600 mm	IEC 61587-1, IEC 61587-2	暗灰色	钢	RAL 7021
21630-881	42 U	800 mm	IEC 61587-1, IEC 61587-2	暗灰色	钢	RAL 7021
21630-882	47 U	600 mm	IEC 61587-1, IEC 61587-2	暗灰色	钢	RAL 7021
21630-883	47 U	800 mm	IEC 61587-1, IEC 61587-2	暗灰色	钢	RAL 7021

Table 3/3	
物料号	防护等级
21630-876	IP20
21630-877	IP20
21630-878	IP20
21630-879	IP20
21630-880	IP20
21630-881	IP20
21630-882	IP20
21630-883	IP20

ADDITIONAL PRODUCT DETAILS

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.