

插排, IEC C19



模块化、紧凑型 PDU，支持多种功能。PDU 采用 1 U x 1 U 铝机箱，可轻松集成在带 IEC C19 插座的机架中。

CERTIFICATIONS



功能

带有 IEC C19 插座的插排

安装时，插排可以向四个方向旋转（90°增量）

连接电缆 2 米, 带符合 IEC 60309 标准的连接器

安装高度 1 U

安装高度1 U

技术参数

Table 1/2

物料号	产品类型	插座类型	Socket Quantity	Switched Outlets	颜色	交流电压
60110-280	插排	IEC C19	8	否	灰色	230V
60110-281	插排	IEC C19	12	否	灰色	230V
60110-282	插排	IEC C19	12	否	灰色	230V

Table 2/2						
物料号	高度	长度	深度	材料	表面处理	包装数量
60110-280	44mm	438.5mm	44mm	铝, 塑料	阳极氧化	1
60110-281	44mm	947.5mm	44mm	铝, 塑料	阳极氧化	1
60110-282	44mm	947.5mm	44mm	铝, 塑料	阳极氧化	1

ADDITIONAL PRODUCT DETAILS

请单独订购垂直安装支架。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com