

CABLE TO WEB OF RAIL MOLD ONLY, SIGNAL



功能

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

技术参数

轨道类型: 85 lb to 141 lb T-Rail Sections

材料: Graphite

Table 1/2						
物料号	绑线终端样式	Handle Clamp	导体公称外径	焊机式样	焊药	方向
SBB200CLH	1" Tab		4.76mm	TB5, T21	SB25, Sold Separately	Left Hand
SBB200CRH	1" Tab		4.76mm	TB5, T21	SB25, Sold Separately	Right Hand
SBW3150BLH	1" Tab	C105B, Sold Separately	4.76mm	TB5	SB25 or SB25PLUSF80, Sold Separately	Left Hand
SBW3150BRH	1" Tab	C105B, Sold Separately	4.76mm	TB5	SB25 or SB25PLUSF80, Sold Separately	Right Hand

物料号	绑线终端样式	Handle Clamp	导体公称外径	焊机式样	焊药	方向
SBB200YLH	1" Tab	C105B, Sold Separately	5.18mm	T21, TB5	SB25 or SB25PLUSF80, Sold Separately	Left Hand
SBB200YRH	1" Tab	C105B, Sold Separately	5.18mm	T21, TB5	SB25 or SB25PLUSF80, Sold Separately	Right Hand
SBB200XRH	1" Tab		6.6mm	TB5, T21	SB32, Sold Separately	Right Hand
SBB200PLH	1" Tab		7.75mm	TB5, T21	SB32, Sold Separately	Left Hand
SBB200PRH	1" Tab		7.75mm	TB5, T21	SB32, Sold Separately	Right Hand
SBWW6LH	Field-made	C105B, Sold Separately	8mm	T21	SB32 or SB25PLUSF80, Sold Separately	Left Hand
SBWW6RH	Field-made	C105B, Sold Separately	8mm	T21	SB32 or SB25PLUSF80, Sold Separately	Right Hand

Table 2/2

物料号	导体尺寸
SBB200CLH	3/16" Bondstrand
SBB200CRH	3/16" Bondstrand
SBW3150BLH	3/16" Bondstrand
SBW3150BRH	3/16" Bondstrand
SBB200YLH	16 mm ² Concentric
SBB200YRH	16 mm ² Concentric
SBB200XRH	25 mm ² Stranded
SBB200PLH	35 mm ² Stranded
SBB200PRH	35 mm ² Stranded
SBWW6LH	50 mm ² Solid

物料号	导体尺寸
SBWW6RH	50 mm ² Solid

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER